

Instructions:

Print out and confirm the scale in both directions.

Cut out along the outer dotted lines. 2.

3.

Optional: Attach to a more rigid surface such as cardboard. Place the template against the inside of the wheel making sure that the 4. hat/bell surface sits flush against the wheel or, if used, wheel spacers.

A minimum of 2.5 mm (.10 in.) clearance is recommend to account for wheel 5. and suspension component flex.

Wheel Clearance Template
BMW F80 M3/4 front
Radi-CAL Competition Package
CP9668 caliper, 372 mm disc

essex parts services, inc. www.essexparts.com

DWG. NO. 1578 REV

Essex package no. 13.01.10046

3